

Flush-type connector - SACC-DSI-M8FS-4CON-M10/0,5 - 1456093

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type socket, 4-pos., M8, rear/screw mounting with M10 thread, with 0.5 m TPE litz wire, 4 x 0.25 mm²

Key commercial data

package_quantity	1
GTIN	4046356605892

Technical data

Dimensions

Length of cable	0.5 m
-----------------	-------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Socket)
Degree of protection	IP67

General

Rated current at 40°C	4 A
Rated voltage	30 V
Number of positions	4
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Individual wires
Mounting type	Rear mounting M10

Material

Inflammability class according to UL 94	HB
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PUR / PA66
Material, knurls	Zinc die-cast, nickel-plated

Flush-type connector - SACC-DSI-M8FS-4CON-M10/0,5 - 1456093

Technical data

Material

Sealing material	Viton
------------------	-------

Cable

Cable type	TPE litz wire
AWG signal line	24
Wire colors	brown, white, blue, black
Conductor material	Tin-plated Cu litz wires
Ambient temperature (operation)	-25 °C ... 90 °C (cable, fixed installation)

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 4.0	EC002061
ETIM 5.0	EC002061

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST /


Approval details

GOST 
--

Drawings

Flush-type connector - SACC-DSI-M8FS-4CON-M10/0,5 - 1456093


Dimensioned drawing



M8 flush-type socket

Flush-type connector - SACC-DSI-M8FS-4CON-M10/0,5 - 1456093


Dimensioned drawing



Mounting panel with feed-through hole

Flush-type connector - SACC-DSI-M8FS-4CON-M10/0,5 - 1456093

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>