

Interface module - UM 45-D25SUB/S/ZFKDS - 2293637

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with spring-cage connection and D-Subminiature pin strip, for mounting on NS 35/7.5, 25-pos.

The illustration shows version UM 45-D 37SUB/S/ZFKDS

Product Features

- 9 to 50-pos.
- Spring-cage connection technology
- According to IEC 60807-2
- 1:1 connection



Key commercial data

package_quantity	1
GTIN	4017918120535

Technical data

Dimensions

Width	90 mm
Height	45 mm
Depth	50 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per branch	2.5 A
Max. current carrying capacity per branch	1.5 A (with even load on all branches)
Number of positions	25
Status display	No
Test voltage	800 V (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 60664

Interface module - UM 45-D25SUB/S/ZFKDS - 2293637

Technical data

General

Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Pollution degree	2
Surge voltage category	II
Rated surge voltage	1.2 kV
Rated insulation voltage	125 V

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Spring-cage connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Stripping length	8 mm

Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB pin strip
Number of positions	25

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
-------------	----------

Interface module - UM 45-D25SUB/S/ZFKDS - 2293637

classifications

UNSPSC

UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

GOST /

Approval details



accessories

Screwdriver tools

SZF 0-0,4X2,5 - 1204504



System cable

CABLE-D25SUB/B/S/ 50/KONFEK/S - 2302120



CABLE-D25SUB/B/S/100/KONFEK/S - 2302133



Interface module - UM 45-D25SUB/S/ZFKDS - 2293637

accessories

CABLE-D25SUB/B/S/150/KONFEK/S - 2302146



CABLE-D25SUB/B/S/200/KONFEK/S - 2302159



CABLE-D25SUB/B/S/300/KONFEK/S - 2302162



CABLE-D25SUB/B/S/400/KONFEK/S - 2302175



CABLE-D25SUB/B/S/600/KONFEK/S - 2302188



CABLE D-SUB-S/.../.../... - 2302340



Interface module - UM 45-D25SUB/S/ZFKDS - 2293637

accessories

CABLE D-SUB-B-B-S/.../.../... - 2302421



CABLE-D-25SUB/F/OE/0,25/S/0,5M - 2926153



CABLE-D-25SUB/F/OE/0,25/S/1,0M - 2926166



CABLE-D-25SUB/F/OE/0,25/S/1,5M - 2926179



CABLE-D-25SUB/F/OE/0,25/S/2,0M - 2926182



Interface module - UM 45-D25SUB/S/ZFKDS - 2293637

accessories

CABLE-D-25SUB/F/OE/0,25/S/3,0M - 2926195



CABLE-D-25SUB/F/OE/0,25/S/4,0M - 2926205



CABLE-D-25SUB/F/OE/0,25/S/6,0M - 2926218




CABLE-D-25SUB-F-OE-0,25-S/... - 2900906



Drawings

Interface module - UM 45-D25SUB/S/ZFKDS - 2293637

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>