

Test plugs - MPS-MT - 0201744

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Test plugs, Color: silver

Product Features

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm or 4 mm diameter
- Two-piece test plug for individual plug color combinations
- The test plugs are inserted in the function shaft of terminal blocks from the CLIPLINE complete system or in the test connections provided
- Individual test adapters can be combined using the modular PS-...2,3MM test plug.

Key commercial data

package_quantity	10
GTIN	4017918098803

Technical data

General

Color	silver
Length	28.5 mm
Length contact range	10.85 mm
Pin diameter	2.30 mm
Note on dimensions	Length without insulating sleeve
Material	silver-plated brass
Minimum temperature	-40 °C
Maximum temperature	125 °C
Voltage	60 V
Current	10 A

classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111

Test plugs - MPS-MT - 0201744

classifications

eCl@ss

eCl@ss 6.0	27141148
eCl@ss 7.0	27141148
eCl@ss 8.0	27141148

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC002255
ETIM 5.0	EC002255

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>