

Snap-in markers - US-EMP (52,5X15) - 0830296

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Snap-in markers, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Snapped into marker carrier, Lettering field: 52.5 x 15 mm

The figure shows a version of the article

Key commercial data

package_quantity	10
GTIN	4046356715706

Technical data

Dimensions

Length (b)	52.5 mm
Height	0.5 mm
Width (a)	15 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10-25 °C / 35-65 % relative humidity. Storage in a cool and dry place is recommended.

General

Color	white
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC
Number of individual labels	16
Number of individual labels per row	2
RoHS compliant	Yes
Printability	Thermal transfer
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed

Snap-in markers - US-EMP (52,5X15) - 0830296

Technical data

General

Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Foil strength	500 µm

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Magazine

THERMOMARK CARD-US-MAG1 - 5146451



Snap-in markers - US-EMP (52,5X15) - 0830296

accessories

Marker carriers

CARRIER-EMP (1000X15) GY - 0829366



CARRIER-EMP (1000X15) TR - 0829530



CARRIER/L-EMP (1000X15) GY - 0829559



CARRIER/L-EMP (1000X15) TR - 0829560



Cover

CARRIER-EMP (1000X15) COVER - 0829520



Drawings

