

Feed-through terminal block - STTB 2,5 OG - 3035373

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Cross section: 0.08 mm² - 4 mm², AWG: 28 - 12, Connection type: Spring-cage connection, Width: 5.2 mm, Color: orange, Mounting type: NS 35/7,5, NS 35/15



Key commercial data

package_quantity	50
GTIN	4046356122795

Technical data

General

Number of levels	2
Number of connections	4
Color	orange
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	22 A
Nominal voltage U _N	500 V
Open side panel	ja

Dimensions

Width	5.2 mm
Length	67.5 mm
Height NS 35/7,5	47.5 mm
Height NS 35/15	55 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
------------------------------------	----------------------

Feed-through terminal block - STTB 2,5 OG - 3035373

Technical data

Connection data

Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Stripping length	10 mm
Internal cylindrical gage	A3

classifications

eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Feed-through terminal block - STTB 2,5 OG - 3035373

approvals

IECEx / ATEX / CSA / UL Recognized / cUL Recognized / LR / GL / BV / DNV / ABS / KR / NK / GOST / VDE Gutachten mit Fertigungsüberwachung / IECCEB CB Scheme / VDE Gutachten mit Fertigungsüberwachung / GOST / cULus Recognized /

Approval details

IECEx	
Nominal voltage UN	440 V
Nominal current IN	19.5 A
mm²/AWG/kcmil	0.08-2.5

ATEX 	
Nominal voltage UN	440 V
Nominal current IN	23.5 A
mm²/AWG/kcmil	0.08-4

CSA 		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	20 A
mm²/AWG/kcmil	28-12	28-12

UL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	20 A	20 A	5 A
mm²/AWG/kcmil	28-12	28-12	28-12

cUL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	20 A	20 A	5 A
mm²/AWG/kcmil	28-12	28-12	28-12

Feed-through terminal block - STTB 2,5 OG - 3035373

approvals

LR

GL	
Nominal voltage UN	500 V
Nominal current IN	24 A
mm²/AWG/kcmil	2.5

BV

DNV

ABS	
Nominal voltage UN	600 V
Nominal current IN	20 A
mm²/AWG/kcmil	26-12

KR

NK

GOST 



VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	500 V
Nominal current IN	24 A
mm²/AWG/kcmil	0.2-2.5

IECEE CB Scheme 	
Nominal voltage UN	500 V
Nominal current IN	24 A
mm²/AWG/kcmil	0.2-2.5

Feed-through terminal block - STTB 2,5 OG - 3035373

approvals

	
Nominal voltage UN	800 V
Nominal current IN	24 A
mm²/AWG/kcmil	0.2-2.5



accessories

End cover

D-STTB 2,5 - 3030459



DP PS-5 - 3036725



Partition plate

ATP-STTB 4 - 3030747



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

Screwdriver tools

SZF 1-0,6X3,5 - 1204517



Marker carriers

STP 5-2 - 0800967



Labeled terminal marker

WST 2,5 - 3030941



ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

UCT-TMF 5 CUS - 0829658



Documentation

ST-IL - 3039900



Bridge

FBS 20-5 - 3030226



FBS 10-5 - 3030213



FBS 5-5 - 3030190



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

FBS 4-5 - 3030187



FBS 3-5 - 3030174



FBS 2-5 - 3030161



FBS 50-5 - 3038930



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZBF 5:UNBEDRUCKT - 0808642



UC-TMF 5 - 0818153



UCT-TMF 5 - 0828744



Insulating sleeve

ISH 2,5/0,2 - 3002843



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

ISH 2,5/0,5 - 3002856



ISH 2,5/1,0 - 3002869



Test plug terminal block

PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

PS-5 - 3030983



PS-5/2,3MM RD - 3038723



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Feed-through terminal block - STTB 2,5 OG - 3035373

accessories

E/UK - 1201442



E/UK 1 - 1201413



Drawings

Circuit diagram

