


## Snap-in markers - UC-EM (20X7) TQ - 0825500

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Snap-in markers, Sheet, turquoise, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snapped into marker carrier, Lettering field: 20 x 7 mm

### Product Features

- ✓ The UC-EM ... UniCard labeling range includes markers for devices and switching devices from a wide range of manufacturers
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The sheets provide space for including function texts

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 10            |
| GTIN             | 4046356364324 |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 20 mm |
| Width (a)  | 7 mm  |

#### Ambient conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -40 °C ... 120 °C           |

#### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Color                                   | turquoise                      |
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | V2                             |
| Material                                | PA                             |
| Number of individual labels             | 20                             |
| Number of individual labels per row     | 5                              |

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |

## Snap-in markers - UC-EM (20X7) TQ - 0825500

### classifications

#### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 5.0</b> | 27149103 |
| <b>eCl@ss 5.1</b> | 27141137 |
| <b>eCl@ss 6.0</b> | 27141137 |
| <b>eCl@ss 7.0</b> | 27141137 |
| <b>eCl@ss 8.0</b> | 27141137 |

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 2.0</b> | EC000761 |
| <b>ETIM 3.0</b> | EC000761 |
| <b>ETIM 4.0</b> | EC000761 |
| <b>ETIM 5.0</b> | EC000761 |

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211811 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121410 |
| <b>UNSPSC 12.01</b>  | 39121410 |
| <b>UNSPSC 13.2</b>   | 39121410 |

### accessories

#### Magazine

P1 UC-MAG 6 - 5146121



---

### Drawings

#### Pictogram

