

## Zack marker sheet - ZBM 5/WH:UNBEDRUCKT - 5061549

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Zack marker sheet, Sheet, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 5.2 mm, Lettering field: 7.5 x 4.6 mm

### Key commercial data

<b>package_quantity</b>	50
<b>GTIN</b>	4017918096496

### Technical data

#### Dimensions

<b>Length (b)</b>	7.5 mm
<b>Width (a)</b>	4.6 mm

#### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-40 °C ... 100 °C

#### General

<b>Note</b>	Can be labeled with CMS
<b>Color</b>	white
<b>Components</b>	free from silicone and halogen
<b>Inflammability class according to UL 94</b>	V2
<b>Material</b>	PA
<b>Number of individual labels</b>	120
<b>Number of individual labels per row</b>	12
<b>Number of marker strips</b>	10

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	24190208
<b>eCl@ss 4.1</b>	24190208
<b>eCl@ss 5.0</b>	27149103
<b>eCl@ss 5.1</b>	27141137
<b>eCl@ss 6.0</b>	27141137
<b>eCl@ss 7.0</b>	27141137

## Zack marker sheet - ZBM 5/WH:UNBEDRUCKT - 5061549

### classifications

#### eCl@ss

eCl@ss 8.0	27141137
------------	----------

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

### accessories

#### Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>