

Plastic label - EMLP (27X12,5)R SR - 0819521

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic label, Roll, silver, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 27 x 12.5 mm

The figure shows a similar product

Product Features

- ✓ Quick and cost-effective labeling with THERMOMARK ... printers
- ✓ High-quality appearance
- ✓ High level of resistance to chemical and mechanical influences
- ✓ The EMLP ... self-adhesive markers are equivalent to engraved labels
- ✓ Primarily used for marking electrical components, devices, and buttons

Key commercial data

package_quantity	1
GTIN	4046356160735

Technical data

Dimensions

Length (b)	27 mm
Width (a)	12.5 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (assembly)	18 °C ... 40 °C

General

Color	silver
Components	free from silicone and halogen
Inflammability class according to UL 94	V0
Material	Polyester
Number of individual labels	500
Number of individual labels per row	2
RoHS compliant	Yes
Adhesive	Acrylic
Printability	Thermal transfer

Plastic label - EMLP (27X12,5)R SR - 0819521

Technical data

General

Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Burning behaviour	self-extinguishing
Foil strength	175 µm
Adhesive strength	400 µm

classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Ink ribbon

Plastic label - EMLP (27X12,5)R SR - 0819521

accessories

THERMOMARK-RIBBON 110 - 5145384



Marker carriers

CARRIER-EMP 22 (27X12,5) - 0827446



CARRIER-EMLP 22 (27X12,5) - 0828985



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>