

# Socket insert - VS-SI-SD-GB - 1656547

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ground contact socket, exclusively for service interface order no. 1656482 and 1656495, plastic, for Great Britain

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356029919

## Technical data

### Mechanical characteristics

<b>Connection method</b>	Screw connection
<b>Conductor cross section</b>	2.5 mm <sup>2</sup>
<b>Connection cross section AWG</b>	14
<b>Color</b>	gray

### Ambient conditions

<b>Ambient temperature (operation)</b>	-10 °C ... 60 °C
<b>Degree of protection</b>	IP20

### Material data

<b>Inflammability class according to UL 94</b>	V0
<b>Housing material</b>	PA

### Electrical characteristics

<b>Rated voltage (III/3)</b>	250 V
<b>Rated current</b>	13 A

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27140815
<b>eCl@ss 4.1</b>	27140815
<b>eCl@ss 5.0</b>	27143423
<b>eCl@ss 5.1</b>	27143423
<b>eCl@ss 6.0</b>	27143423
<b>eCl@ss 7.0</b>	27449001
<b>eCl@ss 8.0</b>	27449001

# Socket insert - VS-SI-SD-GB - 1656547

## classifications

### ETIM

<b>ETIM 2.0</b>	EC001121
<b>ETIM 3.0</b>	EC000125
<b>ETIM 4.0</b>	EC000125
<b>ETIM 5.0</b>	EC000125

### UNSPSC

<b>UNSPSC 6.01</b>	31261501
<b>UNSPSC 7.0901</b>	31261501
<b>UNSPSC 11</b>	31261501
<b>UNSPSC 12.01</b>	31261501
<b>UNSPSC 13.2</b>	31261501


## approvals

---

GOST /

---

### Approval details



## Drawings

Dimensioned drawing

Socket insert

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>