

Cover plate - HC-B 6-AP-GY - 1660368

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON cover plate, for wall cutouts of type B6, 3.5 mm thick, gray

The illustration shows a version of the product

Key commercial data

package_quantity	10
GTIN	4017918022006

Technical data

Dimensions

Length	86 mm
Height	3.5 mm
Hole diameter	4.5 mm
Width	52 mm
Drill hole distance, horizontal	70 mm
Drill hole distance, vertical	32 mm

General

Note	For wall cutouts of type B6
Material	PA
Inflammability class according to UL 94	HB
Color	light gray
Design	B6

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

Cover plate - HC-B 6-AP-GY - 1660368

classifications

ETIM

ETIM 3.0	EC002309
ETIM 4.0	EC000886
ETIM 5.0	EC002314


UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

approvals

GOST /

Approval details



Drawings

Dimensioned drawing

