

N disconnect terminal block - UTN 35 - 3245066

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



N disconnect terminal block, Special and hybrid connection, Cross section: 0.75 mm² - 35 mm², AWG: 18 - 2, Width: 15 mm, Color: blue, Mounting type: NS 35/7,5, NS 35/15

Product Features

- ☒ Same shape as UT standard terminal blocks

Key commercial data

package_quantity	50
GTIN	4046356299039

Technical data

General

Note	Assembly instructions: For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips.
Number of levels	1
Number of connections	2
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V2

General

Maximum load current	110 A (with 35 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	110 A
Nominal voltage U _N	400 V
Open side panel	nein

Dimensions

Width	15 mm
Length	55 mm
Height	49.80 mm

N disconnect terminal block - UTN 35 - 3245066

Technical data

Dimensions

Height NS 35/7,5	51 mm
Height NS 35/15	58.5 mm

Connection data

Note	Terminal point
Conductor cross section solid min.	0.75 mm ²
Conductor cross section solid max.	35 mm ²
Conductor cross section AWG/kcmil min.	18
Conductor cross section AWG/kcmil max	2
Conductor cross section stranded min.	0.75 mm ²
Conductor cross section stranded max.	35 mm ²
Min. AWG conductor cross section, stranded	18
Max. AWG conductor cross section, stranded	2
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	35 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	35 mm ²
2 conductors with same cross section, solid min.	0.75 mm ²
2 conductors with same cross section, solid max.	10 mm ²
2 conductors with same cross section, stranded min.	0.75 mm ²
2 conductors with same cross section, stranded max.	10 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	10 mm ²
Connection method	Special and hybrid connection
Stripping length	16 mm
Screw thread	M6
Tightening torque, min	3.2 Nm
Tightening torque max	3.7 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120

N disconnect terminal block - UTN 35 - 3245066

classifications

eCl@ss

eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000902
ETIM 5.0	EC000902

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Pick-off terminal block

EK 135 - 0401023



EK 116 - 0401010



Support

N disconnect terminal block - UTN 35 - 3245066

accessories

UAB - 3032428



AB/NS - 1201141



AB-UTN 2,5/10 - 3245082



Screwdriver tools

SZS 1,0X6,5 VDE - 1205079



SZS 1,0X4,0 VDE - 1205066



Neutral conductor rail

N disconnect terminal block - UTN 35 - 3245066

accessories

NLS-CU 3/10 SN 1000MM - 0402174



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



N disconnect terminal block - UTN 35 - 3245066

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



N disconnect terminal block - UTN 35 - 3245066

accessories

NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



N disconnect terminal block - UTN 35 - 3245066

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 12:UNPRINTED - 0812120



N disconnect terminal block - UTN 35 - 3245066

accessories

UC-TM 12 - 0819194



UCT-TM 12 - 0829144



Labeled terminal marker

ZB 12 CUS - 0824942



UC-TM 12 CUS - 0824613



UCT-TM 12 CUS - 0829630



End block

N disconnect terminal block - UTN 35 - 3245066

accessories

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Drawings

N disconnect terminal block - UTN 35 - 3245066

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>