

Marker for terminal blocks - TMT 100 R - 0816605

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker for terminal blocks, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Unperforated, Mounting type: Snap into universal marker groove, Snap into flat marker groove, Lettering field: 6.35 x 101.5 mm

The figure shows the TMT 8 R version

Product Features

- ✓ The TMT labeling range includes markers for all products with tall and flat marker grooves
- ✓ Labeling service: Phoenix Contact can custom-label all TMT markers according to your requirements

Key commercial data

package_quantity	1
GTIN	4046356107389

Technical data

Dimensions

Length (b)	6.35 mm
Height	6.4 mm
Width (a)	101.5 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Color	white
Base element material	Polyester foil
Components	free from silicone and halogen
Material	Polyester
Number of individual labels	1000
Number of individual labels per row	1

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208

Marker for terminal blocks - TMT 100 R - 0816605

classifications

eCl@ss

eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Mounting material

TMT TOOL - 0816650



Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



Drawings