



TOOLCRAFT

DATASHEET

Solder Fume Extractor

Item No. 588688

Delivery

- Product with filter installed
- 2x Filters
- Connection piece
- Air deflection hood
- Table clamp
- Operating instructions



Technical data

Product

Input	100 - 240 V/AC 50 - 60 Hz
Power	8 W
Protection class	II
Airflow	120 m ³ /h
Suction	2.5 m/s
Fan speed	3400 rpm
Noise level	50 dB
Operating conditions	-10 to +70 °C, 5 - 95 % RH
Storage conditions	-40 to +85 °C, 5 - 95 %
Dimensions (W x H x D)	210 x 200 x 185 mm
Weight	2320 g (including filters)

Filter

Filter type	Activated carbon
Carbon content	35 - 65 %
Benzene absorption rate	25 - 32 %
Resistance	1 m/s
Dimensions (W x H x D)	130 x 130 x 10 mm

