

Marker cards - SK U/3,8 WH:UNBEDRUCKT - 0803906

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker cards, Sheet, white, Unlabeled, Can be labeled with: Plotter, Office printing systems,
Mounting type: Adhesive, Lettering field: 186 x 3.8 mm

Product Features

- ✓ Labeling service: Phoenix Contact can custom-label SK markers according to your requirements
- ✓ The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- ✓ The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove

Key commercial data

package_quantity	10
GTIN	4017918007799

Technical data

Dimensions

Length (b)	186 mm
Width (a)	3.8 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 150 °C

General

Note	Print image may vary depending on laser printer
Color	white
Components	free from silicone and halogen
Material	Polyester
Number of individual labels	1440
Number of individual labels per row	36
Number of marker strips	40

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103

Marker cards - SK U/3,8 WH:UNBEDRUCKT - 0803906

classifications

eCl@ss

eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Marker pen

B-STIFT - 1051993



Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



Drawings