

OMNILUX UV Tube 18W G13 590x26mm T8

An indispensable means of decoration

Art. No.: 89503005

GTIN: 4026397101751



Features:

- Countless number of application possibilities
- Already existing a good number of years, the "black light effect" is still fascinating: white textiles and objects as well as fluorescent material brightly flash up in darkness!
- Only to be used with ballast resistor
- Easy installation

Logistic

EAN / GTIN: 4026397101751
Weight: 0,12 kg
Length: 0.61 m
Width: 0.03 m
Heigh: 0.03 m

Technical specifications:

Operating voltage:	57 V, AC
Nominal wattage:	18 W
Base:	2 x G-13
Lamp type:	Fluorescent lamp
Beam angle:	360°
Setup:	Easy installation
Color of light:	UV-reflecting
Lead time:	180 s
Construction:	Tube T8
Burning position:	P30 (horizontal ±30°)
Lamp life:	8000 h

Wavelength:	365 nm
Dimensions (LxD):	590x26 mm
Dimensions:	Length: 59 cm Diameter: Ø 2,60 cm
Weight:	110 g
Photobiological safety:	Risk Group 0
Legal specifications	
Special product:	Not designed for household room illumination
Intended use:	Show effect lighting