




## Always ready for the field work

The Eurolite IP FL luminaries are the tools of choice, if you need to light up facades and for general use outdoors. Thanks to the weather resistant housing, it's possible to use the lights even in rain and snow.

There are different devices for different uses: With or without motion detector, a RGB version and one in white. All of them have high lighting power and low consumption.



IP 56

### EUROLITE LED IP FL-8

Brilliant floodlight with LED technology

- Ideal LED luminary for indoor or outdoor use (IP 56)
- 8 x 1 W LED
- Beam angle of 30° or 60°
- 6 different colors available

### Technical specifications:

Power supply:	230 V AC, 50 Hz ~
Power consumption:	13 W
Protection grade:	IP 56
LED type:	1 W
Number of LEDs:	8
Light output intensity:	500 Lm
Dimensions (LxWxH):	50 x 170 x 150 mm
Weight:	1 kg

No. 51914510.....	6400K, 30°
No. 51914515.....	6400K, 60°
No. 51914520.....	3000K, 30°
No. 51914525.....	3000K, 60°
No. 51914527.....	red, 30°
No. 51914528.....	red, 60°
No. 51914530.....	green, 30°
No. 51914531.....	green, 60°
No. 51914533.....	blue, 30°
No. 51914534.....	blue, 60°
No. 51914536.....	yellow, 30°
No. 51914537.....	yellow, 60°