



### Specification

Sound Level	$\geq 90\text{dB}$ at 12VDC/30cm
Resonant Frequency	$2.9 \pm 0.5\text{kHz}$
Input Voltage	3.0 ~ 12 VDC
Tone Nature	Disconnected
Current Consumption	30mA max. at 12VDC
Operating Temperature	$-20 \sim 60^\circ\text{C}$
Operating Humidity	95% RH
Housing material	ABS (Black)
Product weight	approx. 46g

DATE	REVISION	APPROVAL BY	DIMENSION	mm	MODEL	43P29B
			DRAW BY	Oscar Wong	NAME	IP58 Waterproof Buzzer (High dB)
			APPROVAL BY	Rikki So		
			DATE	25-04-13		