

## Product Description

Can be used universally; Fast and easy assembly



## Application range

- In combination with protective conduit
- SILVYN® SI/SP/SP-PU (smooth conduits)
- SILVYN® EL/ELÖ/ELT (corrugated conduits)

## Benefits

- Can be used universally
- Fast and easy assembly

## Design

- Metric connection thread
- Hexagonal collar with integrated conduit connection

## Approvals

- UL FILENUMBER E308201

## Product features

- Dust protection
- Moisture-protection
- High-tensile

**Technical Data****Upon request**

With 45° elbow

Grey, RAL 7001

**Colour delivered**

Black (RAL 9005), UV-resistant

**Material**

PA66 Halogen-free

**Protection rating**

IP 65

**Temperature range**

-50°C to +135°C

**Article List**

Part number	Article designation	Connection thread M	Clear opening (mm)	Suitable for SILVYN® SI	Suitable for SILVYN® SP/SP-PU	SILVYN® EL/ELÖ/ELT	Pieces / PU
SILVYN® MPC-M black							
55502460	SILVYN MPC M16/1	16 x 1.5	8.0	11 x 14		10 x 14,7	10
55502461	SILVYN MPC M16/2	16 x 1.5	11.0	13 x 16	12 x 16	12 x 16,6	10
55502462	SILVYN MPC-M 20/1	20 x 1.5	14.0	13 x 16	12 x 16	12 x 16,6	10
55502463	SILVYN MPC M20/2	20 x 1.5	14.0		16 x 20	16 x 20,7	10
55502464	SILVYN MPC M25	25 x 1.5	19.0		22 x 27	22 x 27,7	10
55502465	SILVYN MPC M32/1	32 x 1.5	23.0			25,0 x 30,6	10
55502469	SILVYN MPC M16/1	M32 x 1.5	25.0			28 x 33,5	10
55502466	SILVYN MPC M40	40 x 1.5	33.0			35 x 41,0	2
55502467	SILVYN MPC M50	50 x 1.5	37.0			40 x 46,4	2
55502468	SILVYN MPC M63	63 x 1.5	48.0		50 x 56	50 x 57,2	1
SILVYN® MPC-M grey							



55502441	SILVYN MPC M16/1	16 x 1.5	8.0	11 x 14		10 x 14.7	10
55502442	SILVYN MPC M16/2	16 x 1.5	11.0	13 x 16	12 x 16	12 x 16,6	10
55502443	SILVYN MPC-M 20/1	20 x 1.5	14.0	13 x 16	12 x 16	12 x 16,6	10
55502444	SILVYN MPC M20/2	20 x 1.5	14.0		16 x 20	16 x 20,7	10
55502445	SILVYN MPC M25	25 x 1.5	19.0		22 x 27	22 x 27,7	10
55502446	SILVYN MPC M32/1	32 x 1.5	23.0			25,0 x 30,6	10
55502447	SILVYN MPC M16/1	M32 x 1.5	25.0			28 x 33,5	10
55502448	SILVYN MPC M40	40 x 1.5	33.0			35 x 41,0	2
55502449	SILVYN MPC M50	50 x 1.5	37.0			40 x 46,4	2
55502439	SILVYN MPC M63	63 x 1.5	48.0		50 x 56	50 x 57,2	1

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.