






DATA SHEET	5550 2460
SILVYN® MPC M	valid from : 25.07.2011

The SILVYN® MPC M is a polyamide conduit gland for smooth and corrugated conduits.
The hexagonal body with integrated conduit connection enables best assembling.



Dimensions table:

Part No. RAL 9005	Part No. RAL 7001	Connection- Thread	Clear Opening mm
5550 2460	5550 2441	M16x1,5/1	8,0
5550 2461	5550 2442	M16 x1,5/2	11,0
5550 2462	5550 2443	M20 x1,5/1	11,0
5550 2463	5550 2444	M20 x1,5/2	14,0
5550 2464	5550 2445	M25 x1,5	19,0
5550 2465	5550 2446	M32 x1,5/1	23,0
5550 2469	5550 2447	M32 / 2	25,0
5550 2466	5550 2448	M40 x1,5	33,0
5550 2467	5550 2449	M50 x1,5	37,0
5550 2468	5550 2439	M63 x1,5	48,0

Part No. RAL 9005	Part No. RAL 7001	Connection- Thread	 Suitable conduit SILVYN® SI	 Suitable conduit SILVYN® SP/ SP-PU	 Suitable conduit SILVYN® EL/ELÖ/ELT
5550 2460	5550 2441	M16x1,5/1	11 x 14		10 x14,7
5550 2461	5550 2442	M16 x1,5/2	13 x 16	12 x 16	12 x16,6
5550 2462	5550 2443	M20 x1,5/1	13 x 16	12 x 16	12 x16,6
5550 2463	5550 2444	M20 x1,5/2		16 x 20	16 x20,7
5550 2464	5550 2445	M25 x1,5		22 x 27	22 x 27,7
5550 2465	5550 2446	M32 x1,5/1			25,0 x 30,6
5550 2469	5550 2447	M32 / 2			28 x 33,5
5550 2466	5550 2448	M40 x1,5			35 x 41
5550 2467	5550 2449	M50 x1,5			40 x 46,4
5550 2468	5550 2439	M63 x1,5			50 x 57,2



DATA SHEET	5550 2460
SILVYN[®] MPC M	valid from : 25.07.2011

Material:
Body PA halogen-free

Resistance:
UV- resistant
Oil- resistant

Features:
Dust protection
Moisture protection
Tensile strength

Colour:
black
grey

Protection Class:
IP 65

Temperature range:
-50°C up to +135°C

Norm references:

