



<b>DATA SHEET</b>	52107800
<b>SKINDICHT® RWV-M</b>	valid from : 19.06.2006

The SKINDICHT® RWV-M is a cast zinc cable gland with 90° elbow. The locknut enables the angle gland to be secured in any position.



**The gland make-up consists of:**

Angle housing	cast zinc
Washer	galvanized steel
Pressure screw	nickel-plated brass
Locknut	nickel-plated brass
Indented sealing ring	elastomer
O – ring	elastomer

**Technical features:**

Connecting thread:	M 12- M 40 in accordance to EN 60 423
IP protection:	IP 55 in acc. to EN 60 529
Temperature range:	- 20°C to + 100°C

For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M.Zankl	Document: DB52107800_1EN	page 1 of 1
----------------------------------	--------------------------	-------------