

## Product Description

Enables the use of cable glands with smaller connection threads than the existing threaded holes



## Application range

---

- Machines
- Devices
- Housings

## Benefits

---

- Enables the use of cable glands with smaller connection threads than the existing threaded holes

## Design

---

- Metric connection thread acc. to EN 50262



**Technical Data**

**Upon request**

Also available with pre-installed O-ring

**Temperature range**

-60°C to +200°C

**Material**

Nickel-plated brass

**Article List**

Part number	Thread/ male M1	Thread/ female M2	Pieces / PU
SKINDICHT® MR-M			
52104310	16 x 1.5	12 x 1.5	100
52104311	20 x 1.5	12 x 1.5	100
52104312	20 x 1.5	16 x 1.5	100
52104313	25 x 1.5	16 x 1.5	50
52104314	25 x 1.5	20 x 1.5	50
52104315	32 x 1.5	20 x 1.5	50
52104316	32 x 1.5	25 x 1.5	50
52104317	40 x 1.5	25 x 1.5	25
52104318	40 x 1.5	32 x 1.5	25
52104319	50 x 1.5	32 x 1.5	25
52104320	50 x 1.5	40 x 1.5	10
52104321	63 x 1.5	40 x 1.5	10
52104322	63 x 1.5	50 x 1.5	10

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.