



DATA SHEET	52104980
SKINDICHT® SVRE-M	valid from : 10.11.2008

The SKINDICHT® SVRE-M brass cable gland with hexagonal fitting, variable incised sealing ring and metric connecting thread, test in acc. with EN 50262. The incised sealing ring allows the cable gland to adapt to the relevant cable diameter. As a result fewer sizes need to be kept in stock, bringing a significant cost advantage.



Components:

Body:	nickel plated brass
Compression screw:	nickel plated brass
Flat washer:	steel zinc plated
Incised steel:	elastomer

Technical feature:

Connecting thread:	M16x1.5 – M63x1.5 in acc. to EN 60 423
Functions thread:	PG- thread in acc. to DIN 40430
Protection class:	IP 54
Temperature range:	- 20°C bis +80C°

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M. Steinberg	document: DB52104980EN	page 1 von 1
---------------------------------------	------------------------	--------------