

Product Description

Enables the use of cable glands with smaller connection threads than the existing threaded holes



Application range

- Machines
- Devices
- Housings

Benefits

- Enables the use of cable glands with smaller connection threads than the existing threaded holes

Design

- Metric connection thread acc. to EN 50262



Technical Data

Colour delivered

Light grey (RAL 7035)

Temperature range

-40°C to +100°C

Material

Polyamide, glass fibre-reinforced

Article List

Part number	Thread/ male M1	Thread/ female M2	SW (mm)	Pieces / PU
SKINDICHT® KU-M light grey				
52104505	16 x 1.5	12 x 1.5	22	100
52104470	20 x 1.5	12 x 1.5	24	100
52104504	20 x 1.5	16 x 1.5	24	100
52104472	25 x 1.5	12 x 1.5	29	100
52104473	25 x 1.5	16 x 1.5	29	100
52104474	25 x 1.5	20 x 1.5	29	100
52104475	32 x 1.5	12 x 1.5	36	50
52104476	32 x 1.5	16 x 1.5	36	50
52104477	32 x 1.5	20 x 1.5	36	50
52104478	32 x 1.5	25 x 1.5	36	50
52104479	40 x 1.5	16 x 1.5	46	50
52104480	40 x 1.5	20 x 1.5	46	50
52104481	40 x 1.5	25 x 1.5	46	25
52104482	40 x 1.5	32 x 1.5	46	25
52104483	50 x 1.5	20 x 1.5	55	5
52104484	50 x 1.5	25 x 1.5	55	5
52104485	50 x 1.5	32 x 1.5	55	5
52104486	50 x 1.5	40 x 1.5	55	5
52104487	63 x 1.5	25 x 1.5	68	5
52104488	63 x 1.5	32 x 1.5	68	5
52104489	63 x 1.5	40 x 1.5	68	5
52104469	63 x 1.5	50 x 1.5	68	5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.