

Product Description

Fast mounting; Easy to disassemble; Tear-proof connection; No slack in the conduit; No loose parts



Application range

- In combination with protective conduit
- SILVYN® SPLIT
- Fastening of conduits on machine walls for all applications

Benefits

- Fast mounting
- Easy to disassemble
- Tear-proof connection
- No slack in the conduit
- No loose parts

Design

- One-piece conduit holder with M4/M5/M6 borehole for fixation

Note

- UV-resistant and weather-resistant

Product features

- One-piece conduit holder



Technical Data

Colour delivered

Black (RAL 9005), UV-resistant

Temperature range

-40°C to +120°C

Material

Halogen-free PA

Article List

Part number	Article designation	Conduit size (mm)	For conduit with outer Ø (mm)	Suitable for SILVYN® SPLIT	Pieces / PU
SILVYN® SPLIT COS					
61806690	10	8,9/13,6	13.6	10	100
61806700	14	12,9/18,7	18.7	14	100
61806710	20	19,8/25,9	25.9	20	50
61806720	23	23,7/31,3	31.3	23	50
61806730	37	31,7/41,9	41.9	37	20
61806740	45	43,1/54,2	54.2	45	20

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.