

Product Description

Fast assembly; Easy to disassemble; High-tensile; High sealing performance; Can be rotated



Application range

- In combination with protective conduit
- SILVYN® RILL PA6
- SILVYN® RILL PA12
- Robot-building
- Rotating applications

Benefits

- Fast assembly
- Easy to disassemble
- High-tensile
- High sealing performance
- Can be rotated

Design

- Metric connection thread
- Body with inner sealing
- Upper part with snap-in sleeve

Approvals

- UL FILENUMBER E308201



Note

- For rotating applications, disassemble the upper part to remove sealing, then re-assemble.

Technical Data

Colour delivered

Grey (RAL 7001) Black (RAL 9005), UV-resistant

Material

PA6

Protection rating

IP 68

IP 69K according to DIN 40050 T.9

Temperature range

-40 °C to +115 °C

Article List

Part number	Connection thread M	Hole Ø (mm)	For conduit with outer Ø (mm)	Thread length/ D (mm)	SW (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK-GM grey							
55501000	10 x 1.0	6.5	10.0	12.0	17	6,5 x 10,0	50
55501010	12 x 1.5	8	13.0	12.0	20	10 x 13,0	50
55501020	16 x 1.5/1	10	13.0	12.0	20	10 x 13,0	50
55501030	16 x 1.5/2	12	15,8	12.0	23	12 x 15,8	50
55501040	20 x 1.5/1	12	15,8	13.0	23	12 x 15,8	50
55501050	20 x 1.5/2	16	21,2	13.0	29.5	16,5 x 21,2	50
55501060	25 x 1.5	20.5	28,5	13.0	37	23 x 28,5	25
55501070	32 x 1.5	27.5	34,5	15.0	44	29 x 34,5	25
55501080	40 x 1.5	35	42,5	15.0	51.5	36 x 42,5	25
55501090	50 x 1.5	45	54,5	15.3	65.5	48 x 54,5	10
55500990	63 x 1.5	48	54,5	16.0	59	48 x 54,5	10
SILVYN® KLICK-GM black							
55501005	10 x 1.0	6.5	10.0	12.0	17	6,5 x 10,0	50
55501015	12 x 1.5	8	13.0	12.0	20	10 x 13,0	50
55501025	16 x 1.5/1	10	13.0	12.0	20	10 x 13,0	50
55501035	16 x 1.5/2	12	15,8	12.0	23	12 x 15,8	50
55501045	20 x 1.5/1	12	15,8	13.0	23	12 x 15,8	50



55501055	20 x 1.5/2	16	21,2	13.0	29.5	16,5 x 21,2	50
55501065	25 x 1.5	20.5	28,5	13.0	37	23 x 28,5	25
55501075	32 x 1.5	27.5	34,5	15.0	44	29 x 34,5	25
55501085	40 x 1.5	35	42,5	15.0	51.5	36 x 42,5	25
55501095	50 x 1.5	45	54,5	15.3	65.5	48 x 54,5	10
55500995	63 x 1.5	48	54,5	16.0	59	48 x 54,5	10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.