

Product Description

Fast assembly; High-tensile; Sealing; Vibration protection



Application range

- In combination with protective conduit
- SILVYN® FPAS
- Applications with strong vibrations

Benefits

- Fast assembly
- High-tensile
- Sealing
- Vibration protection

Design

- Metric connection thread
- Body
- Upper part with integrated all-round tooting

Approvals

- UL FILENUMBER E308201
- UNDERGROUND



Product features

- In black colour UV-resistant and weather-proofed
- Removeable with a screwdriver

Technical Data

Colour delivered

Black (RAL 9005), UV-resistant Grey (RAL 7001)

Material

PA66 Halogen-free

Protection rating

IP 66

Temperature range

-40°C to +135°C

Article List

Part number	Article designation	For conduit with outer Ø (mm)	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAG-M black				
55506305	M12x1,5	10.0	10	10
55506315	M16x1,5/1	13.0	13	10
55506325	M16x1,5/2	15,8	16	10
55506335	M20x1,5/1	15,8	16	10
55506345	M20x1,5/2	21,2	21	10
55507055	M20x1,5/3	18,5	18	10
55506355	M25x1,5	28,5	28	10
55506365	M32x1,5	34,5	34	10
55506375	M40x1,5	42,5	42	2
55506385	M50x1,5/1	42,5	42	2
55506395	M50x1,5/2	54,5	54	2
55506405	M63x1,5/1	54,5	54	2
55506475	M63x1,5/2	67,2	67	2
SILVYN® FPAG-M grey				
55506300	M12x1,5	10.0	10	10
55506310	M16x1,5/1	13.0	13	10
55506320	M16x1,5/2	15,8	16	10
55506330	M20x1,5/1	15,8	16	10



55506340	M20x1,5/2	21,2	21	10
55507050	M20x1,5/3	18,5	18	10
55506350	M25x1,5	28,5	28	10
55506360	M32x1,5	34,5	34	10
55506370	M40x1,5	42,5	42	2
55506380	M50x1,5/1	42,5	42	2
55506390	M50x1,5/2	54,5	54	2
55506400	M63x1,5/1	54,5	54	2
55506470	M63x1,5/2	67,2	67	2

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.