

SKINTOP® halogen-free

### Product Description

Maximum reliability;Extremely flame-retardant according to UL 94V-0;Completely halogen-free (including sealing material);Self-extinguishing, no dripping;Permanent vibration protection



### Application range

- When the protection of people and property is a priority.
- Public buildings
- Ventilation systems
- Tunnel construction
- Underground railways and trains

### Benefits

- Maximum reliability
- Extremely flame-retardant according to UL 94V-0
- Completely halogen-free (including sealing material)
- Self-extinguishing, no dripping
- Permanent vibration protection



## Design

- Metric connection thread acc. to EN 50262

## Technical Data

### Caution

Refer to Appendix T21 for the installation dimensions and torques

### Colour delivered

Light grey (RAL 7035)

### Material

Polyamide UL 94V-0 - halogen-free Sealing ring:  
LSE 1 - halogen-free O-ring: LSE 1 - halogen-free

### Tests

Filament wire test EN 60695-2-1/1 +960°C

### Protection rating

IP 68 - 5 bar

### Temperature range

-20°C to +100°C

## Article List

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINTOP® ST-HF-M						
53111407	ST-HF-M 12 x 1,5	4-5,5	15	30.0	8.0	100
53111417	ST-HF-M 16 x 1,5	4,5-9	19	34.0	8.0	100
53111427	ST-HF-M 20 x 1,5	7-13	25	37.0	9.0	100
53111437	ST-HF-M 25 x 1,5	9-17	30	40.0	10.0	50
53111447	ST-HF-M 32 x 1,5	11-21	36	47.0	10.0	25
53111457	ST-HF-M 40 x 1,5	19-28	46	52.0	10.0	10
53111467	ST-HF-M 50 x 1,5	27-35	55	62.0	12.0	5
53111477	ST-HF-M 63 x 1,5	34-45	66	71.0	12.0	5

### Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.