

Product Description

For closing pre-threaded holes; Assembling with screwdriver



Application range

- Machine and equipment manufacturing
- Electric motor manufacturing

Benefits

- For closing pre-threaded holes
- Assembling with screwdriver

Design

- Metric connection thread acc. to EN 50262



Technical Data

Upon request

Fitted with FKM O-ring

Material

Dummy plug: nickel-plated brass O-ring: NBR

Protection rating

IP 54 IP 68 with O-ring

Temperature range

With O-ring: -30°C to +100°C Without O-ring: -60°C to +200°C

Article List

Part number	Article designation / size	Outer Ø (mm)	Pieces / PU
SKINDICHT® BL-M			
52103100	12 x 1,5	14.0	100
52103110	16 x 1,5	18.0	100
52103120	20 x 1,5	22.0	100
52103130	25 x 1,5	28.0	100
52103140	32 x 1,5	35.0	50
52103150	40 x 1,5	44.0	25
52103160	50 x 1,5	54.0	10
52103170	63 x 1,5	70.0	10
SKINDICHT® BL-M with O-ring			
52103105	12 x 1,5	14.0	100
52103115	16 x 1,5	18.0	100
52103125	20 x 1,5	22.0	100
52103135	25 x 1,5	28.0	100
52103145	32 x 1,5	35.0	50
52103155	40 x 1,5	44.0	25
52103165	50 x 1,5	54.0	10
52103175	63 x 1,5	70.0	10
52103190	75 x 1,5	80.0	1

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.