


TITLE: Cat. 6 (1/0.51BC*1P+A)*4+TEAR LINE SSTP



ITEMS		UNIT	A (4P)			
CONDUCTOR	SIZE	AWG	24AWG			
	CONSTRUCTION	PCS/mm	1/0.510±0.008mm			
	MATERIAL	/	BC			
	PICKS	mm	/			
INSULATION	MATERIAL	/	FPE			
	DIA.	mm	1.21±0.05mm	1.21±0.05mm	1.21±0.05mm	1.21±0.05mm
	COLOR	/	BLUE/WHITE	ORANGE/WHITE	GREEN/RED	BROWN/WHITE
	CONCENTRIC	%	≥90%	≥90%	≥90%	≥90%
(TWIST)	CONSTRUCTION	/	S=24mm	S=30mm	S=27mm	S=35mm
	AL-FOIL	mm u	AL-FOIL			
	MYLAR	mm u	/			
	Back twist rate	%	/	/	/	/
	Aluminum foil conductive surface	/	向外			
	OVERLAPPING	%	30%	30%	30%	30%
	DIA.	mm	2.42±0.05mm	2.42±0.05mm	2.42±0.05mm	2.42±0.05mm
(TWIST)	CONSTRUCTION	/	S			
	MO/OVERLAPPING	mm u %	/			
	DRAIN WIRE	mm	/			
	AL-FOIL OVERLAPPING	mm u %	/			
	Aluminum foil conductive surface	/	/			
	FILL	/	TEAR LINE			
	DIA.	/	5.5±0.2mm			
(BRAID/SHIELD)	CONSTRUCTION	/	0.120±0.008mm/5*16=80# AL-MG			
	PICKS	mm	41±1mm			
Jacket	MATERIAL	/	PVC			
	OD.	mm	8.5±0.2mm			

VIEW:



*NOTE:

1BLUE/WHITE, 2ORANGE/WHITE, 3GREEN/RED, 4BROWN/WHITE

NOTE:

1. Impedance (ohms) 100±15 ohms

Artikel: 601881