

Product Description

One seal for several clamping ranges; Rings can be individually adapted to various cable diameters



Application range

- Incised sealing ring for SKINDICHT® cable glands

Benefits

- One seal for several clamping ranges
- Rings can be individually adapted to various cable diameters

Note

- Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit



Technical Data

Colour delivered

Black

Material

CR

Temperature range

-20°C to +80°C

Article List

Part number	Article designation / size	Outer Ø x holes (mm)	Thickness (mm)	Pieces / PU
SKINDICHT® E-M				
52100620	E-M 12	10 x 5	5.0	250
52100621	E-M 16	13,8 x 3/6/9	5,5	250
52100622	E-M 20	17,6 x 4/7/10/13	6.0	250
52100623	E-M 25	22,6 x 8.5/11.5/14.5/17.5	7,5	100
52100624	E-M 32	29,6 x 16/19/22/25	9,5	100
52100625	E-M 40	37,6 x 23/26/29/32	12.0	50
52100626	E-M 50	47,6 x 30/33/36/39	14.0	50
52100627	E-M 63	60,6 x 36/39/42/45	14.0	50

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.