

Product Description

Protection against mechanical stress; Protection against dust; Protection against humidity; Low abrasion protection



Application range

- Cable protection
- Additional insulation
- Bundling and guiding of cables and wires

Benefits

- Protection against mechanical stress
- Protection against dust
- Protection against humidity
- Low abrasion protection

Design

- Hard PVC inner spiral
- Soft PVC outer sheath

Note

- Black (RAL 9005) is available upon request



Product features

- Flexible
- Dimensionally stable

Technical Data

Colour delivered

Silver grey (RAL 7001)

Temperature range

-15 °C to +60 °C

Material

Soft PVC with hard PVC spiral, SBR/NBR

Article List

Part number	Internal Ø x external Ø (mm)	Bending radius (mm)	Inner Ø (mm)	Suitable for SILVYN® SSV-M/SSVZ-M	Suitable for SILVYN® USK-M	Suitable for SILVYN® SSV/SSVZ	Suitable for SILVYN® USK	Suitable for SILVYN® SCH	PU ring (m)
SILVYN® SP									
61714000	10 x 14	50	10	16.1 / 16/9/10	12 x 1,5	9,1	9	10 - 16 S	25
61714010	12 x 16	60	12	16.2 / 16/9/12	16 x 1,5	9,2	11	12 - 20 S	25
61714020	14 x 18	70	14	20.1 / 20/11/14		11,1	13,5	12 - 20 S	25
61714100	16 x 20	70	16	- / 20/11/16	20 x 1,5	11,2	16	16 - 25 S	25
61714110	22 x 27	90	22	25 / 20/16/22	25 x 1,5	16,1	21	20 - 32 S	25
61714120	30 x 36	140	30	32 / 32/29/30	32 x 1,5	29,1	29	25 - 40 S	25
61714070	38 x 44	190	38	40 / 40/36/38	40 x 1,5	36,1	36	32 - 50 S	25
61714090	50 x 56	270	50	63 / 63/48/50	50 x 1,5	48,1	48	40 - 60 S	25

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.