

Product Description

Fast and easy assembly;Vibration protection;High-tensile;Can be rotated



Application range

- In combination with protective conduit
- SILVYN® FPS
- SILVYN® FD-PU
- Robot-building
- For rotating applications

Benefits

- Fast and easy assembly
- Vibration protection
- High-tensile
- Can be rotated

Design

- Metric connection thread
- Swivelling upper part with integrated inner sleeve

Product features

- Smooth inner surface
- Slim construction



Technical Data

Colour delivered
Silver grey (RAL 7001)
Material
PP

Protection rating
IP 54
Temperature range
-10 °C to +110 °C

Article List

Part number	Connection thread M	Clear opening (mm)	Overall length/ C (mm)	Thread length/ D (mm)	SW (mm)	Suitable for SILVYN® FPS/FD-PU	Pieces / PU
SILVYN® LKI-M							
55501400	12 x 1.5	5.5	38.0	10.0	16	7 x 10	50
55501410	16 x 1.5	9.5	39.5	10.0	19	10 x 14	50
55501420	20 x 1.5	11.5	42.0	10.0	22	13 x 17	50
55501430	25 x 1.5	14.5	48.0	11.0	27	16 x 21	50
55501440	32 x 1.5	19.5	58.0	12.0	35	22 x 27	25
55501450	40 x 1.5	27.0	59.0	12.0	45	29 x 36	25
55501460	50 x 1.5	35.5	62.5	12.0	54	38 x 45	25
55501470	63 x 1.5	46.0	68.0	15.0	65	48 x 56	10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.