

Product Description

Fast assembly; Easy to disassemble; Tear-proof connection; No slack in the conduit



Application range

- In combination with protective conduit
- SILVYN® RILL PA6
- SILVYN® RILL PA12
- Fastening of conduits on machine walls for all applications

Benefits

- Fast assembly
- Easy to disassemble
- Tear-proof connection
- No slack in the conduit

Design

- Multi-part conduit holder with M5 borehole for fixation

Note

- For black (RAL 9005), replace the last digit of the part no. with "5".

Product features

- Impact-resistant polyamide



Technical Data

Colour delivered

Grey (RAL 7001) Black (RAL 9005), UV-resistant

Temperature range

-30°C to +70°C

Material

PA6

Article List

Part number	PG size	Pieces / PU
SILVYN® KLICK-S grey		
61811110	7	100
61811120	9	100
61811130	11	50
61811190	13.5	50
61811140	16	50
61811150	21	50
61811160	29	30
61811170	36	20
61811180	48	20

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.