



For more Information
please call

1-800-Belden1



Description:

22 AWG stranded (7x29) .031" bare compacted copper conductor, gas-injected foam HDPE insulation, tinned copper/bare copper double braid shield (95% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	22	7x29	BCC - Bare Compacted Copper	0.7874

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	3.683

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)	Dia. (mm)	Description
1	Braid	TC - Tinned Copper	94	4.2418	Layer 1
2	Braid	TC - Tinned Copper	94	4.8006	Layer 2

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 6.147 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -35°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 59.528 Kg/Km

Max. Recommended Pulling Tension: 400.338 N

Min. Bend Radius (Install)/Minor Axis: 60.960 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

CEC/C(UL) Specification: CM

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

RG Type: 59/U

Flame Test

UL Flame Test: UL1685 UL Loading

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes - Black Only

Suitability - Aerial: Yes - Black only, when supported by a messenger wire

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.308414

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

55.777

Nominal Velocity of Propagation:

VP (%)

80

Nominal Delay:

Delay (ns/m)

4.2653

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

40.0282

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

7.8744

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

1.000	0.656
3.600	1.641
5.000	1.969
6.000	2.198
7.000	2.395
10.000	2.953
12.000	3.215
25.000	4.725
67.500	7.874
71.500	8.203
88.500	9.187
100.000	9.843
135.000	11.484
143.000	11.812
180.000	13.452
270.000	16.733

360.000	19.686
540.000	24.279
720.000	28.545
1000.000	34.451
750.000	29.201
1500.000	43.637
2000.000	51.512
2250.000	55.449
3000.000	66.604

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination.

Other Electrical Characteristic 2: Return Loss tested in accordance with ASTM D-4566 paragraph 45.3, using a 75 Ohm fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	850.000	20.000
851.000	4500.000	15.000

Sweep Test

Sweep Testing: 100% Sweep tested 5 MHz to 4.5 GHz.

Notes (Overall)

Notes: Compacted conductor combines impedance uniformity of solid conductors and "nick-resistance" of stranded conductor.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1505F B591000	305 MT	20.412 KG	BLACK, MATTE	C	#21 GIFHDLDPPE DBLB PVC
1505F G7V1000	305 MT	20.412 KG	RED, MATTE	C	#21 GIFHDLDPPE DBLB PVC
1505F G7W1000	305 MT	20.412 KG	GREEN, MATTE	C	#21 GIFHDLDPPE DBLB PVC
1505F G7X1000	305 MT	20.412 KG	BLUE, MATTE	C	#21 GIFHDLDPPE DBLB PVC
1505F G7Y1000	305 MT	20.412 KG	WHITE, MATTE	C	#21 GIFHDLDPPE DBLB PVC
1505F G8L1000	305 MT	20.412 KG	ORANGE, MATTE	C	#21 GIFHDLDPPE DBLB PVC
1505F Z4B1000	305 MT	20.412 KG	VIO Z4B		#21 GIFHDLDPPE DBLB PVC
1505F 0041000	305 MT	20.412 KG	YELLOW	C	#21 GIFHDLDPPE DBLB PVC

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 8 Revision Date: 03-03-2009

© 2008 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.