

## Product Description

Protection against dust; Protection against humidity; Low abrasion protection



## Application range

- Easy cable protection
- Additional insulation
- Bundling and guiding of cables and wires

## Benefits

- Protection against dust
- Protection against humidity
- Low abrasion protection

## Design

- Soft-PVC conduit

## Product features

- Flexible
- Soft



Technical Data

Note

Flame-retardant and self-extinguishing Dielectric strength: 25 kV/mm Tear-resistance: 23 N/mm<sup>2</sup> Shore A hardness: 75 °C to 90 °C

Colour delivered

Silver grey (RAL 7001)

Material

Soft PVC

Temperature range

-5°C to +80°C

Article List

Part number	Internal Ø x external Ø (mm)	Inner Ø (mm)	Suitable for SILVYN® SSV-M/SSVZ-M	Suitable for SILVYN® SSV/SSVZ	Suitable for SILVYN® SCH	PU ring (m)
SILVYN® SI						
61713210	7 x 9	7	12.1/-		10 - 16 S	50
61713240	9 x 12	9	12.2/-			50
61713270	11 x 14	11	16.1 / -		10 - 16 S	50
61713300	13 x 16	13	16.2 / -		12 - 20 S	50
61713330	14 x 18	14	20.1 / 20/11/14		12 - 20 S	50
61713360	18 x 22	18	20.3 / 20/13/18	13,5.1	16 - 25 S	50
61713390	23 x 28	23	25 / 25/21/24	21,1	25 - 40 S	50
61713420	32 x 38	32	32 / 32/29/32	29,2	32 - 50 S	50

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.