


CR TYPE



ITEM NO.	A ϕ	B ϕ	C
CR-07P	7.4 \pm 0.4	10.2 \pm 0.4	2.60
CR-11SP	10.7 \pm 0.4	14 \pm 0.4	1.1
CR-11P	10.7 \pm 0.4	16.0 \pm 0.4	3.30
CR-13P	13.8 \pm 0.4	17.5 \pm 0.4	3.1
CR-15P	15.0 \pm 0.4	19.5 \pm 0.4	3.50
CR-17P	17.2 \pm 0.4	22.0 \pm 0.4	3.1
CR-19P	19.3 \pm 0.4	23.8 \pm 0.4	3.50
CR-22P	21.2 \pm 0.4	25.8 \pm 0.4	3.10
CR-24P	24.3 \pm 0.4	32.0 \pm 0.4	3.61
CR-25P	25.0 \pm 0.4	30.0 \pm 0.4	4.10
CR-28P	28.0 \pm 0.4	34.0 \pm 0.4	3.10
CR-32P	31.2 \pm 0.4	40.0 \pm 0.4	4.12
CR-35P	34.9 \pm 0.4	42.0 \pm 0.4	3.1
CR-40P	39.6 \pm 0.5	50.0 \pm 0.5	4.85
CR-48P	47.5 \pm 0.4	54.5 \pm 0.5	2.0
CR-52P	52.0 \pm 0.5	60.0 \pm 0.5	5.8
CR-62P	62.0 \pm 0.5	76.0 \pm 0.5	5.8
CR-80P	80.0 \pm 0.5	89.0 \pm 0.5	5.8



		MATERIAL	ITEM NO.
		P.P.	CR TYPE
SCALE		FINISH	NAME
			FLEXIBLE CONDUIT
\triangle	(. .)	TOLERANCE \pm 0.5mm	\triangle 03-24-2009 DATE REVISIONS K003
			R.NO.

