



Name	Material	Specification
Conductor	CCS	10/0.1 x 12
Dielectric	PVC	∅1.0±0.05 x 12
Shielded	CCS	22/0.10 braid x 12
Ground wire	PVC	7/0.10 x 1
Jacket	PVC	∅2.2±0.1 x 28.6±1.3 Black

		DESCRIPTION		SCART CABLE			
		CABLE No.		SH10-3004			
DRAW		DWG. No.		2006/12/21		REV.	A
CHECK		DATE				SCALE	1:1
APP.		SIZE	A4	UNIT	mm	SHEET	1/1