

Housing design H-B. The industry standard.

Product Description

The housing standard. Wide choice for all applications



Application range

- Plant engineering
- Light & sound technology
- Plastics industry

Benefits

- The housing standard. Wide choice for all applications

Product features

- Hood, low version
- Reels for single lever
- Straight cable entry
- Versions with / without neck



Technical Data

Material

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel Sealing: NBR

Protection rating

IP 65 (latched)

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

Article List

| Part number | Article | M | PG | Neck | Pieces / PU |
|--|------------------|----|----|------|-------------|
| H-B housing: hood (straight cable entry, bolts for single lever) | | | | | |
| 10080900 | H-B 16 TG-RO 21 | | 21 | yes | 5 |
| 19080900 | H-B 16 TG-RO M25 | 25 | | | 5 |

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.