

DATASHEET

Coaxial Cable RG58

Version 11/17

Item no. 605517



Construction.....Ø0.8mm CCS+Ø3.0mm FOAM PE+ AL Foil+112X0.12mm
 Conductor..... Al-Mg Alloy Wire Braiding+Ø5.0mm PVC sheath
 OD:0.8 mm CCS
 Dielectric..... OD:3.0mm Foam Polythene
 Sheath inside..... Aluminum Foil
 Braiding.....112x0.12 Aluminum-Magnesium Alloy Wire Braiding
 SheathOD:5.0mm ROHS PVC
 Rated Voltage.....48V DC
 Electrical Properties.....Nominal Impedance: 50+/-2 OHM
Nom. Capacitance: 48 pF/m
Screening Factor: >52 db
Nominal Velocity of Propagation: 68 %

Max. Att	MHz	5	55	211	450	600	750	778	865	1000	1350	2279.32
(dB/100m)	dB	10.6	15.04	18.41	22.83	25.86	28.68	29.29	30.87	33.44	39.4	52.83