



## YDRQ2.E325250 Tubing, Mechanical Protection and Fittings - Component

[Page Bottom](#)

### Tubing, Mechanical Protection and Fittings - Component

[See General Information for Tubing, Mechanical Protection and Fittings - Component](#)

**HELLERMANN TYTON GMBH**

E325250

GROSSER MOORWEG 45

25436 TORNESCH, GERMANY

Cat. No.	Max Working Temp, °C	Indoor Use	Outdoor Use
<b>Thermoplastic nonmetallic mechanical protection Type C corrugated tubing</b>			
HG-SW16, HG-SW18, HG-SW20, HG-SW21, HG-SW25, G-SW28, HG-SW34, HG-SW42, HG-SW54, HG-SW67, HG-LW16, HG-LW18, HG-LW20, HG-LW21, HG-LW25, HG-LW28, HG-LW34, HG-LW42, HG-LW54, HG-LW67, HG-HW16, HG-HW18, HG-HW20, HG-HW21, HG-HW25, HG-HW28, HG-HW34, HG-HW42, HG-HW54, HG-FR16, HG-FR18, HG-FR20, HG-FR21, HG-FR25, HG-FR28, HG-FR34, HG-FR42, HG-FR54, HG-HI16, HG-HI18, HG-HI20, HG-HI21, HG-HI25, HG-HI28, HG-HI34, HG-HI42, HG-HI54, HG-HI67, HG-HIW16, HG-HIW18, HG-HIW20, HG-HIW21, HG-HIW25, HG-HIW28, HG-HIW34, HG-HIW42, HG-HIW54, PSR12, PSRO12, PSRH12, PSR16, PSRO16, PSRH16, PSR20, PSRO20, PSRH20, PSR25, PSRO25, PSRH25, PSR30, PSRO30, PSRH30, PSR32, PSRO32, PSRH32, PSR40, PSRO40, PSRH40, PSR50, PSRO50, PSRH50, PSR63, PSRO63, PSRH63			
	105	Yes	-

Cat. No.	Indoor Dry Locations	Liquid-tight Locations
<b>45 degree elbow fittings</b>		
PSR16-45-M20, PSR20-45-M20, PSR25-45-M25, PSR32-45-M32	Yes	-
<b>90 degree elbow fittings</b>		
PSR16-90-M16, PSR16-90-M20, PSR20-90-M20, PSR25-90-M25, PSR32-90-M32, PSR40-90-M40		
	Yes	-
<b>Fittings</b>		
PSR12-S-M16, PSR16-S-M16, PSR16-S-M20, PSR20-S-M20, PSR25-S-M25, PSR30-S-M32, PSR32-S-M32, PSR40-S-M40, PSR50-S-M50, PSR63-S-M63		
	Yes	-
<b>Fittings with PG or NPT thread (black or gray)</b>		
HG-S, HGL-S, HG-90, HGL-90, HG-45, HGL-45, HG-HG, HGL-HGL, HG-T, HGL-T, HG-Y, HGL-Y		
	Yes	-

Marking: Company name and model designation.

[Last Updated](#) on 2016-07-29

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2017 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2017 UL LLC".



## YDRQ8.E325250

## Tubing, Mechanical Protection and Fittings Certified for Canada - Component

[Page Bottom](#)

## Tubing, Mechanical Protection and Fittings Certified for Canada - Component

[See General Information for Tubing, Mechanical Protection and Fittings Certified for Canada - Component](#)

HELLERMANN TYTON GMBH

E325250

GROSSER MOORWEG 45

25436 TORNESCH, GERMANY

Cat. No.	Max Working Temp, °C	Indoor Use	Outdoor Use	FT-4
<b>Thermoplastic nonmetallic mechanical protection Type C corrugated tubing</b>				
HG-SW16, HG-SW18, HG-SW20, HG-SW21, HG-SW25, G-SW28, HG-SW34, HG-SW42, HG-SW54, HG-SW67, HG-LW16, HG-LW18, HG-LW20, HG-LW21, HG-LW25, HG-LW28, HG-LW34, HG-LW42, HG-LW54, HG-LW67, HG-HW16, HG-HW18, HG-HW20, HG-HW21, HG-HW25, HG-HW28, HG-HW34, HG-HW42, HG-HW54, HG-FR16, HG-FR18, HG-FR20, HG-FR21, HG-FR25, HG-FR28, HG-FR34, HG-FR42, HG-FR54, HG-HI16, HG-HI18, HG-HI20, HG-HI21, HG-HI25, HG-HI28, HG-HI34, HG-HI42, HG-HI54, HG-HI67, HG-HIW16, HG-HIW18, HG-HIW20, HG-HIW21, HG-HIW25, HG-HIW28, HG-HIW34, HG-HIW42, HG-HIW54, PSR12, PSRO12, PSRH12, PSR16, PSRO16, PSRH16, PSR20, PSRO20, PSRH20, PSR25, PSRO25, PSRH25, PSR30, PSRO30, PSRH30, PSR32, PSRO32, PSRH32, PSR40, PSRO40, PSRH40, PSR50, PSRO50, PSRH50, PSR63, PSRO63, PSRH63				
	105	Yes	-	-

Cat. No.	Indoor Dry Locations	Liquid-tight Locations
<b>45 degree elbow fittings</b>		
PSR16-45-M20, PSR20-45-M20, PSR25-45-M25, PSR32-45-M32	Yes	-
<b>90 degree elbow fittings</b>		
PSR16-90-M16, PSR16-90-M20, PSR20-90-M20, PSR25-90-M25, PSR32-90-M32, PSR40-90-M40		
	Yes	-
<b>Fittings</b>		
PSR12-S-M16, PSR16-S-M16, PSR16-S-M20, PSR20-S-M20, PSR25-S-M25, PSR30-S-M32, PSR32-S-M32, PSR40-S-M40, PSR50-S-M50, PSR63-S-M63		
	Yes	-
<b>Fittings with PG or NPT thread (black or gray)</b>		
HG-S, HGL-S, HG-90, HGL-90, HG-45, HGL-45, HG-HG, HGL-HGL, HG-T, HGL-T, HG-Y, HGL-Y		
	Yes	-



Marking: Company name, model designation and the Recognized Component Mark for Canada, CRL.

[Last Updated](#) on 2016-07-29

[Questions?](#)
[Print this page](#)
[Terms of Use](#)
[Page Top](#)

© 2017 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2017 UL LLC".