

**Sheathed bell cable YR-DR**  
**Datasheet**

Item No.	Sheathed bell cable YR-DR	Sheathed bell cable YR-DR	Sheathed bell cable YR-DR
B/N	<b>606477</b>	<b>607065</b>	<b>607475</b>
Jacker, outer dimension	PVC 4mm	PVC 5.8mm	PVC 7.9mm
Cross section area	2 x 0.5 sqmm	6 x 0.5 sqmm	12 x 0.5 sqmm
strand per conductor	2 x 0.8 mm	6 x 0.8 mm	12 x 0.8 mm
Conductor material	CCA	CCA	CCA
color	WHITE	WHITE	WHITE
Packaging	20 meter spool	20 meter spool	20 meter spool
Capacitance	75pF	75pF	75pF
Wire resistance	90.2ohm/KM	90.2ohm/KM	90.2ohm/KM

**Technical Data**

Material of the jacket : PVC  
 Conductor resistance (Ohm/km): Max 57.5 ohm/m  
 Insulation resistance: Min 200M ohm x km  
 Rated voltage: 48V  
 Operating temperature: -20 to +70 C