

## Connectors, reducers and couplers

• HG-Y Y-Connector, IP66

## **Features and Benefits**

- Fast fit Y-connector
- Branches reduce conduit size
- High pull-off strength
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus

Technical Table								
			Entry nominal	Exit nominal				
	Article-No.	Туре	diameter	diameter	Pack Cont.			
	166-25801	HG16-Y13	16	13	5			
	166-25802	HG21-Y16	21	16	3			
	166-25803	HG28-Y21	28	21	3			
	166-25804	HG34-Y28	34	28	2			

All dimensions in mm. Subject to technical changes.

Colour grey available on request.



HelaGuard HG-Y, Y-Connector, IP66.

Polyamide 6.6 (PA66)
Black (BK)
-50 °C to +135 °C
UL94 V2

## • HGL-Y Y-Connector, IP68

Fulfils IP66, IP67, IP68 and IP69k.

## **Features and Benefits**

- Fast fit Y-connector
- Branches reduce conduit size
- High pull-off strength
- $\bullet$  Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus

Technical Table								
		_	Entry nominal	Exit nominal				
	Article-No.	Туре	diameter	diameter	Pack Cont.			
	166-25901	HGL16-Y13	16	13	5			
	166-25902	HGL21-Y16	21	16	3			
	166-25903	HGL28-Y21	28	21	3			
	166-25904	HGL34-Y28	34	28	2			

All dimensions in mm. Subject to technical changes.

Colour grey available on request.



HelaGuard HGL-Y, Y-Connector with conduit seals.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.

