

Product Description

Protection against dust; Additional abrasion protection for critical areas; Cut into length without frizzle on the conduit's end; Simple, fast cable bundling



Application range

- Easy cable protection
- Additional insulation
- Bundling and guiding of cables and wires
- Rodent-protection

Benefits

- Protection against dust
- Additional abrasion protection for critical areas
- Cut into length without frizzle on the conduit's end
- Simple, fast cable bundling

Design

- Polyester - PET with shrinkable Polyolefin fibres

Product features

- Abrasion-resistant
- Flexible
- Shrinkable
- Shrinking ratio: 2:1
- Maximum length lost after shrinkage is less than 15 %



Technical Data

Upon request

Bulk containers on rolls

Note

No dielectric strength

Self-extinguishing according to DIN

75200/FMVSS302 and DIN5510

Colour delivered

Black (RAL 9005), UV-resistant

Material

Polyamide 6.6 - halogen-free

Temperature range

-55°C to +125°C

Article List

Part number	D (mm)	Clamping range (mm)
SILVYN® SHRINK BRAID PET		
61721270	27.0	6 - 12
61721271	48.0	12 - 25
61721272	56.0	15 - 30
61721274	115.0	35 - 70
61721273	86.0	25 - 50

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.