



## Fittings for metallic conduits

### • SC-PC Plain Hole Connector

Plain hole connector, nickel plated brass.

#### Features and Benefits

- Two part fitting comprising shell and body without thread
- Body is fitted to the conduit through the opposite side of the entry
- Acts as a locking device
- Provides a smooth entry bush



HelaGuard SC-PC Plain Hole Connector.

Technical Table

Article-No.	Type	Nominal Ø	Pack Cont.
166-30500	SC10-PC	10	10
166-30501	SC12-PC	12	10
166-30502	SC16-PC	16	10
166-30503	SC20-PC	20	10
166-30504	SC25-PC	25	10
166-30505	SC32-PC	32	2
166-30506	SC40-PC	40	2
166-30507	SC50-PC	50	1
166-30508	SC63-PC	63	1
166-30509	SC75-PC	75	1

All dimensions in mm. Subject to technical changes.

Material Data

Material	Nickel Plated Brass (NPB)
Colour	Metal (ML)
Operating Temperature	-100 °C to +300 °C



### • SC-FF Fixed Internal Thread

Fixed internal thread, nickel plated brass.

#### Features and Benefits

- Two part fitting comprising shell and body with internal thread
- Can be used to couple two pieces of conduit together when used with a swivel fitting



HelaGuard SC-FF Fixed Internal Thread.

Technical Table

Article-No.	Type	Nominal Ø	Thread Size (metric)	Pack Cont.
166-30600	SC16-FF-M20	16	M20	10
166-30601	SC20-FF-M20	20	M20	10
166-30602	SC25-FF-M25	25	M25	10
166-30603	SC32-FF-M32	32	M32	2

All dimensions in mm. Subject to technical changes.