



BN	<b>608388</b>	<b>608712</b>	<b>609059</b>	<b>609360</b>
Item No.	<b>CONTROL Cable</b>	<b>CONTROL Cable</b>	<b>CONTROL Cable</b>	<b>CONTROL Cable</b>
Jacker, outer dimension	PVC 2mm	PVC 2mm	PVC 2mm	PVC 2mm
No. of conductors	24x 0.2 mm	24x 0.2 mm	24x 0.2 mm	24x 0.2 mm
strand per conductor	0.75 sqmm	0.75 sqmm	0.75 sqmm	0.75 sqmm
color	RED	BLACK	BLUE	YELLOW
Material	Tinned copper	Tinned copper	Tinned copper	Tinned copper
Packaging	blue spool	blue spool	blue spool	blue spool
Length	100 meter	100 meter	100 meter	100 meter

BN	<b>609699</b>	<b>609956</b>	<b>606312</b>	<b>607038</b>
Item No.	<b>CONTROL Cable</b>	<b>CONTROL Cable</b>	<b>CONTROL Cable</b>	<b>CONTROL Cable</b>
Jacker, outer dimension	PVC 2mm	PVC 2mm	PVC 2mm	PVC 2mm
No. of conductors	24x 0.2 mm	24x 0.2 mm	24x 0.2 mm	24x 0.2 mm
strand per conductor	0.75 sqmm	0.75 sqmm	0.75 sqmm	0.75 sqmm
color	BROWN	GREEN-YELLOW	GREEN	GREY
Material	Tinned copper	Tinned copper	Tinned copper	Tinned copper
Packaging	blue spool	blue spool	blue spool	blue spool
Length	100 meter	100 meter	100 meter	100 meter

BN	<b>607427</b>	<b>607783</b>	<b>608390</b>
Item No.	<b>CONTROL Cable</b>	<b>CONTROL Cable</b>	<b>CONTROL Cable</b>
Jacker, outer dimension	PVC 2mm	PVC 2mm	PVC 2mm
No. of conductors	24x 0.2 mm	24x 0.2 mm	24x 0.2 mm
strand per conductor	0.75 sqmm	0.75 sqmm	0.75 sqmm
color	ORANGE	WHITE	VIOLET
Material	Tinned copper	Tinned copper	Tinned copper
Packaging	blue spool	blue spool	blue spool
Length	100 meter	100 meter	100 meter

## Technical Data

Conductor material : tinned-copper  
 Insulation material (with thickness): PVC 0.5mm  
 Core diameter 0.2mm  
 conductor resistance (Ohm/km): Max 29 ohm/km  
 Insulation resistance: Min 200M ohm x km  
 maximum dielectric strength: 1500V / AC  
 temperature range: -20 to +70 C  
 rated voltage: 48V  
 conductor structure: twisted  
 type of flammability: IEC60332-1/EN50265-2-1