

Insert strip - PABT 15X4 WH/200 - 0812175

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Insert strip, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, Mounting type: Insert, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm

Key commercial data

package_quantity	1
GTIN	4017918945664

Technical data

Dimensions

Length (b)	15 mm
Width (a)	4 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Color	white
Inflammability class according to UL 94	V0
Material	Polyester
Number of individual labels	7500
Number of individual labels per row	6

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
----------	----------

Insert strip - PABT 15X4 WH/200 - 0812175

classifications

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>