

**WALL MOUNTING WATERTIGHT MODULAR ENCLOSURE - IP65 - GREY RAL 7035****620 SERIES**

Article		Description- external dimensions (BxHxD)	UM	Packaging
<b>EC62004</b>		Modular enclosure 4 modules dim. 150x170x100 mm	PCS	1/22
<b>EC62008</b>		Modular enclosure 8 modules dim. 200x180x100 mm	PCS	1/14
<b>EC62012</b>		Modular enclosure 12 modules dim. 280x220x100 mm	PCS	1/8
<b>EC62024</b>		Modular enclosure 24 (2x12) modules dim. 290x390x140 mm	PCS	1/4
<b>EC62036</b>		Modular enclosure 36 (2x18) modules dim. 400x400x140 mm	PCS	1/4
<b>EC62054</b>		Modular enclosure 54 (3x18) modules dim. 400x600x140 mm	PCS	1
<b>EC62072</b>		Modular enclosure 72 (4x18) modules dim. 420x885x150 mm	PCS	1

- *Modular distribution enclosures system, wall and flush mounting type, standard and design type. - From 2 to 72 DIN EN50022 modules*
- *Material: made of ABS technopolymer with high resistance to UV rays. - Standard colours: grey RAL 7035, white RAL9001, black RAL7021.*
- *Protection degree from IP40 up to IP65, with plastic caps for the holes of the fixing screws in the back to gain double insulation.*
- *Shock resistance: IK 08 (up to 6j).*
- *Resistance to abnormal heat: up to 650°C (Glow Wire Test, IEC 695-2-1 standard).*
- *Removable door, reversing front.*
- *The support of DIN rail in the flush mounting enclosure allow to compensate for the variable thickness of the plaster in order to align the devices at the correct depth.*
- *Made in compliance with: IEC 60670-1/24, CEI 23-48, CEI 23-49-V1/2000-V2/2003 standards.*