


DIN 6930 T2-m
Extract

NOTE : 1) Mat. DX51D+Z/ZF 275 NA C Mat. quality acc. EN10142
Mat. number 1.0226
Mat. tol. acc. EN10143
2) Dimensions without tol. indication acc. DIN 6930 T2-m

| Nominal value | Tol. |
|---------------|------|
| 1-6 | ±0.2 |
| up6-10 | ±0.3 |
| up10-25 | ±0.4 |
| up25-63 | ±0.5 |
| up63-160 | ±0.6 |

| | | | |
|--------------|----------|--------------------------|-----|
| D | | | |
| C | | | |
| B | | | |
| A | | | |
| INDEX | DATE | MODIFICATION DESCRIPTION | PAR |
| Scale: 1,000 | DATE | NAME | PAR |
| DRAWN | 26/03/13 | DP | |
| CHECKED | | | |
| APPROVED | | | |



ROFIX
BEVESTIGINGEN
FIXATIONS
BEFESTIGUNGEN
FASTENINGS

Industrieterrein
"Teutelberg"
Boslaan 63
3650 Dilsen-Stokkem

TITLE Perforated steel band
Plastified 14mm
Feature hole \varnothing 5,2mm

| | |
|-------------|------------|
| ARTICLE NR. | |
| MATERIAL | 1.0226 |
| TREATMENT | Plastified |
| COMMENT | |
| SIZE | A 4 |
| DRAWING NR. | 6691 |