

DIGITUS® CAT 6, High Density Patch Panel, unshielded



✓ High Density - only 0.5U

✓ Category 6

✓ Unshielded, 24-port

✓ Color black (RAL 9005)

Abstract

DIGITUS® CAT 6 High Density Patch Panel, unshielded, rack mount, 0.5U, 24-port

Features

- CAT 6
- 24x RJ45 jacks, 8P8C
- Height unit: Only 0.5U
- Unshielded
- inclusive dust protection shutters
- Manufactured acc. to Link Performance Class E, for up to 250MHz, EN 50173 and ISO/IEC 11801
- Cable installation via LSA strips, color coded acc. EIA/TIA 568 A&B
- Fixing option for cable ties, central ground connection
- Suitable for 483 mm (19") rack mount

Product Overview


The DIGITUS® 24-port 0.5U Patch Panel offers a high density.

As the panel is only 0.5U in height, it allows to present 48 ports on 1U (2 panels with 24 ports each) which can be installed.

Product Images



Technical Drawings



Product Number Information

DN-91624U-SL-SH DIGITUS® CAT 6 Patch Panel, unshielded, 24-port RJ45, incl. shutter, 8P8C, LSA, 0.5U, 19" rack mount, color black (RAL 9005)

More High Density Patch Panel DIGITUS®

DN-91624S-SL-SH DIGITUS® CAT 6 Patch Panel, shielded, 24-port RJ45, incl. shutter, 8P8C, LSA, 0.5U, 19" rack mount, color black (RAL 9005)

DN-91624S-SL-SH-G DIGITUS® CAT 6 Patch Panel, shielded, 24-port RJ45, incl. shutter, 8P8C, LSA, 0.5U, 19" rack mount, color grey (RAL 7035)

DN-91624S-SL-EA DIGITUS® CAT 6_A, Class E_A High Density Patch Panel, shielded, 0.5U, 24-port, RJ45, incl. dust protection shutter, 8P8C, color black (RAL 9005)

Product Number Information - Accessories

DN-LSA-PT DIGITUS® LSA Punch Down Tool

DN-94014 DIGITUS® Pliers, cutting area 0.7 mm hole, for precise and easy cutting, compact design, with ergonomic handle (yellow)

DN-94015 DIGITUS® Cutter & Stripper, 5" electrical cutter & stripper for flush cutting, size 20-24 AWG

DN-CT-10M-20 Velcro Tape, 20 mm wide, for structured cabling, 10 m roll, color black