

Art.No.	article name
143800015	PRCD-S, mobile protective device, 3-pole, 0,03A, with extension and carrying case, plug and coupling (solid rubber)

PRCD-S, with protective conductor monitoring, 3-pole switching, residual current 0,03A, type A, 230V, 16A, 50Hz, IP44, in solid case, plug (solid rubber) and coupling (solid rubber) with cover, cable lengths: 150cm plug, 300cm coupling, Cable: H07RN-F3G1,5mm²



Technical data		143800015
Voltage type	AC Hz	
Rated insulation voltage Ui	1500 V	
Number of poles	3	
Rated fault current	0.03 A	
Surge current capacity	0.025 kA	
Pollution degree	2	
Connectable conductor cross section multi-wired	1,50 2,50 mm²	
With interlocking device	no	
Additional equipment possible	no	
Mounting method	Cable	
Rated current	16.00 A	
Rated voltage	230 V	
Explosion-proof	no	
Ambient temperature during operating	-25 40 °C	
Rated impulse withstand voltage Uimp	2.50 kV	
Degree of protection (IP)	IP44	
Leakage current type	A	
Frequency	50 Hz	
Short-time delayed tripping	no	
Short-circuit breaking capacity (Icw)	1.500 kA	
Selective protection	no	
Packaging break	J	